

Garant

Indexable insert for turning VNMG 160408, for medium machining, Grade: HB7120-1

**Order data**

Order number	251804 HB7120-1
GTIN	4045197820105
Item class	21G

Technical description

Feed f	0.1 - 0.5 mm/rev.
Main application	M
Corner radius	0.8 mm
Grade	HB7120-1
Chip breaker	VM
Cutting conditions	continuous
Cutting speed v_c main application	80 - 260 m/min
Cutting depth a_p	0.5 - 4 mm
Finishing/roughing assignment	Skrubbearbejdning-sletbearbejdning
Tool material	Carbide

ISO code indexable insert	VNMG 160408
Number of changes/inserts	4
Tolerance	M
Type of product	Indexable insert for turning