

**Garant**
**"5 in 1" drilling and turning tool 1.5×D, left-hand, Ø DC: 8mm**

**Order data**

Order number	268464 8
GTIN	4045197470072
Item class	21K

**Description**
**Version:**

With internal cooling.

Plain shank.

**Application:**

Face turning, longitudinal turning, drilling, internal longitudinal turning, countersinking.

**Note:**

- **Choose corner radii as large as possible.**
- **Always use internal cooling for drilling (at least 5 bar).**

**Technical description**

Bore Ø tolerance D	0/+0.22 mm
Pack of insert screws	269028 30
Shank Ø D <sub>s</sub>	12 mm
Indexable insert No. 268472 – 268496	WCHX 0401..
Nominal Ø D	8 mm
Reach L <sub>1</sub>	12 mm
Overall length L	80 mm
Series	"5 in 1"
Application type	left-hand
Through-coolant	yes

Type of product	Boring bar
-----------------	------------

---

## Accessories

Set of insert screws Type 30	269028 30
Torque screwdriver with scale, to take interchangeable blades maximum torque 200 cNm	659957 200
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX6	674248 TX6