

Garant**Indexable insert for turning TCMT 16T308, for medium machining, Grade: HB7120-1****Order data**

Order number	260988 HB7120-1
GTIN	4045197818775
Item class	21G

Technical description

Cutting speed v_c main application	80 - 260 m/min
Cutting depth a_p	0.5 - 2.5 mm
Chip breaker	VM
Corner radius	0.8 mm
Grade	HB7120-1
Cutting conditions	continuous
Feed f	0.1 - 0.4 mm/rev.
Main application	M
Finishing/roughing assignment	Skrubbearbejdning-sletbearbejdning
Tool material	Carbide
ISO code indexable insert	TCMT 16T308
Number of changes/inserts	3

Tolerance	M
Type of product	Indexable insert for turning