

Garant

Indexable insert for turning WCHX 10T308, for "5 in 1" turning and boring tools, Type: SM

**Order data**

Order number	268494 SM
GTIN	4045197470966
Item class	21K

Description**Suitable for:**

Boring tool No. 268463 – 268468, size 20.

Technical description

Corner radius	0.2 mm
Main application	P
Type	SM
Cutting speed v_c secondary application	110 - 140 m/min
Secondary application	M
Cutting speed v_c main application	110 - 220 m/min
Grade	HB7120
Tool material	Carbide
ISO code indexable insert	WCHX 10T308
Number of changes/inserts	3

suitable for tool dia. D_c

20 mm

Type of product

Indexable insert for turning