


Garant

Indexable insert for turning WCHX 10T304, for "5 in 1" turning and boring tools, Type: ALU


Order data

Order number	268492 ALU
GTIN	4045197470881
Item class	21K

Description
Suitable for:

Boring tool No. 268463 – 268468, size 20.

Technical description

Main application	N
Cutting speed v_c secondary application	180 m/min
Cutting speed v_c main application	300 - 600 m/min
Corner radius	0.2 mm
Type	ALU
Secondary application	K
Grade	HU70AL
Tool material	Carbide
ISO code indexable insert	WCHX 10T304
Number of changes/inserts	3

suitable for tool dia. D_c

20 mm

Type of product

Indexable insert for turning