



## External micrometer with disc anvils, Measuring range: 50-75mm



### Order data

Order number	423000 50-75
GTIN	4045197204028
Item class	42B

### Description

#### Version:

With large-area, hardened disc anvils. Forged and enamelled frame.  
Design with rotating spindle.

#### Application:

For determining the tooth widths of spur and helical gears from module 0.8.

#### Supplied with:

From size 25-50 including 1 setting standard.

### Technical description

Parallelism of the measuring faces	5 µm
Micrometer barrel graduations	1/50 mm
Measuring range	50 - 75 mm
Spindle Ø	8 mm
Spindle pitch	0.5 mm
Disc anvil Ø	20 mm
Scale divisions	0.01 mm
Calibration	B2
Standard	DIN 863
Measurement technology	analogue

Packaging	sturdy box
Type of product	External micrometer

## Services

Calibration External micrometer including setting dimension maximum measuring range 100 mm	022040 100
DAkkS calibration External micrometer including setting dimension maximum measuring range 100 mm	022050 100

## Accessories

Micrometer setting standard overall length 50 mm	421100 50
--	-----------