



Pull stud 45° sealed, without bore, suitable for steep tapers: 30



Order data

Order number	308760 30
GTIN	4045197648013
Item class	32Z

Description

Description:

The toolholder is securely pulled into the spindle by the spindle's clamping gripper using the pull stud. Pull studs come in different versions. They are an important link between the machine and tool. Stringent requirements apply for the accuracy, strength and reliability of pull studs.

Application:

For tools with taper shanks see also **JIS B 6339 (MAS-BT) / ISO 7388-2**.

Note:

Sealed – with O-ring.

Look in the eShop – you will find the right clamping wrench and width for every job.

When installing the pull stud, cheque the correct tightening torque.

Technical description

L ₁	23 mm
suitable for steep tapers	30
maximum tightening torque	20 Nm
Thread M	M12
suitable for taper arbors with colour code	SK 30
Overall length L	43 mm
Head Ø D ₁	11 mm
Collar Ø D	16.5 mm

Width across flats	13 mm
Hole characteristics	without bore
Pull stud standard	MAS 403
Type of product	Pull Stud

Accessories

Wrench for pull studs ISO 7388 suitable for ISO taper size 30	308835 30
---	-----------