

**Garant****Abrasive cap holder, Head Ø, head length, shape: 0713G****Order data**

Order number	553100 0713G
GTIN	4045197330475
Item class	51E

**Description****Version:**

The seamlessly formed abrasive caps slide on to the rubber body and are securely held in place by centrifugal force when the machine is running. **Abrasive caps can be replaced quickly and easily** (replace in direction of slots).

**Slotted, resilient rubber body** with steel shank.

**Application:**

Used mostly in tool making for finishing where access is difficult.

**Suitable for:**

Abrasive caps No. 553035 – 553328.

**Technical description**

Head Ø	7 mm
maximum speed	65000 min <sup>-1</sup>
Shank Ø	3 mm
Head length	13 mm
Type of product	Abrasive cap holders