

Garant**Burr Z5 – fine, Carbide, Type: D0605****Order data**

| | |
|--------------|---------------|
| Order number | 540400 D0605 |
| GTIN | 4045197155429 |
| Item class | 51D |

Description**Version:**

Shank Ø 6 mm.

GARANT burrs are manufactured from high performance carbide grades with high wear resistance and maximum cutting edge strength, using only the latest CNC machines. Steel shanks are used when the head diameter is larger than the shank diameter, otherwise they are made from solid carbide. **Ball shape** (KUD)

Application:

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning, weld and surface preparation.

Technical description

| | |
|---------------------------|------------------------|
| Shape description | Ball |
| Toothing grit designation | fine |
| Tooth type abbreviation | Z5 |
| Head Ø | 6 mm |
| Overall length | 50 mm |
| Shape | D0605 |
| Shank Ø | 6 mm |
| Head length | 5 mm |
| Series | Tooth configuration Z5 |

| | |
|-----------------|---------|
| Tool material | Carbide |
| Type of product | Burr |

User data

| | Suitability | V_c | ISO code |
|--------------------------------|---|----------------------|-----------------|
| Steel < 900 N/mm ² | suitable | | |
| Steel < 1400 N/mm ² | suitable | | |
| Steel < 55 HRC | suitable | | |
| Steel < 60 HRC | suitable only under restricted conditions | | |
| INOX | suitable only under restricted conditions | | |
| Ti | suitable only under restricted conditions | | |
| GG(G) | suitable only under restricted conditions | | |