


**Garant**
**WNMG 060408, Grade: HB7120-1**


## Order data

Order number	252064 HB7120-1
GTIN	4045197820167
Item class	21G

## Description

WN.G 060408 HB7120-1 Grade: HB7120-1  
 Chip breaker: VM  
 Tolerance: M  
 Cutting depth  $a_p$ : 0.5 - 4 mm  
 Feed  $f$ : 0.1 - 0.5 mm/rev.  
 Cutting speed  $v_c$  main application: 80 - 260 m/min

## Technical description

Feed $f$	0.1 - 0.5 mm/rev.
Chip breaker	VM
Cutting depth $a_p$	0.5 - 4 mm
Grade	HB7120-1
Cutting speed $v_c$ main application	80 - 260 m/min
Main application	M

Corner radius	0.8 mm
Cutting conditions	continuous
Finishing/roughing assignment	Semi-roughing
Tool material	Carbide
ISO code indexable insert	WNMG 060408
Number of changes/inserts	6
Tolerance	M
Type of product	Indexable insert for turning