

Garant
Burr Z5 – fine, Carbide, Type: F0618

Order data

| | |
|--------------|---------------|
| Order number | 540400 F0618 |
| GTIN | 4045197521569 |
| Item class | 51D |

Description
Version:

 Shank \varnothing 6 mm.

GARANT burrs are manufactured from high performance carbide grades with high wear resistance and maximum cutting edge strength, using only the latest CNC machines. Steel shanks are used when the head diameter is larger than the shank diameter, otherwise they are made from solid carbide. **Round arch shape** (RBF).

Application:

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning, weld and surface preparation.

Technical description

| | |
|---------------------------|------------------------|
| Toothing grit designation | fine |
| Overall length | 50 mm |
| Tooth type abbreviation | Z5 |
| Shape description | round arch |
| Head \varnothing | 6 mm |
| Shape | F0618 |
| Shank \varnothing | 6 mm |
| Head length | 18 mm |
| Series | Tooth configuration Z5 |
| Tool material | Carbide |

Type of product

Burr

User data

| | Suitability | V_c | ISO code |
|--------------------------------|---|----------------------|-----------------|
| Steel < 900 N/mm ² | suitable | | |
| Steel < 1400 N/mm ² | suitable | | |
| Steel < 55 HRC | suitable | | |
| Steel < 60 HRC | suitable only under restricted conditions | | |
| INOX | suitable only under restricted conditions | | |
| Ti | suitable only under restricted conditions | | |
| GG(G) | suitable only under restricted conditions | | |