

**Garant**
**Face mill arbor vibration damped, BT 40 A = 200, Spigot Ø d1: 27mm**

**Order data**

Order number	303050 27
GTIN	4045197821645
Item class	31A

**Description**
**Version:**

- **Cylindrical form.**
- **Taper shank, spigot, and all contact surfaces are ground at the collar.**
- **With RFID/Balluffchip bore.**
- **Larger collar contact face.**
- **Vibration damped version, arbor with vibration-damping core.**

**Advantage:**

Significantly lower tendency to vibrate. Considerable increase in feed rate.

**Supplied with:**

Cutter lock screw and drive dog.

**Optional extras:**

Special toggle spanner No. 309840.

**Note:**

Further sizes on request.

**Technical description**

Overhang dimension A	200 mm
Milling mandrel length L <sub>4</sub>	21 mm
External Ø D	58 mm
Spigot Ø d <sub>1</sub>	27 mm
Adapter	BT 40 A = 200
Standard	DIN 6357
Arbor standard	DIN 69893

Arbor standard	JIS B6339
Arbor standard	JIS B6339
Shape	A
Balance quality G at rotational speed	G 6.3 at 8,000 rpm
Concentricity	≤ 6 µm
Machining strategy	HPC
Vibration	damped
Type of product	Milling head arbor

## Accessories

Pull stud 90°sealed suitable for steep tapers 40	308790 40
Pull stud 60°sealed suitable for steep tapers 40	308785 40
Pull stud 45°sealed suitable for steep tapers 40	308765 40
Pull stud Hurco 90° with fitsealed suitable for steep tapers 40	308806 40
Pull stud 45°sealed suitable for steep tapers 40	308760 40
Pull stud Hurco 45° with fitsealed suitable for steep tapers 40	308802 40
Pull stud 90°sealed suitable for steep tapers 40	308795 40
Hurco 45° pull stud with 4-mm bore and fitsealed suitable for steep tapers 40	308801 40