

HOLEX

**Abrasive roll, conical (A) 150 grit fine, Abrasive roll Ø× abrasive roll length:
10X25mm**



Order data

Order number	553895 10X25
GTIN	4045197524645
Item class	52E

Description

Version:

Abrasive roll consisting of wound abrasive cloth with **Aluminium Oxide (A)**.
Conical shape for restricted places.

Suitable for:

Abrasive roll holder No. 553835.

Suitable for:

Holder mounting Ø × overall length: 3×63

Technical description

Grit	150
Sander roller Ø	10 mm
Sander roller length	25 mm
maximum speed	26000 min ⁻¹
Grit designation	fine
Grinding media	Standard Aluminium Oxide
Grinding medium code	A
Sander roller form	conical
Type of product	Abrasive roll

User data

	Suitability	V _c	ISO code
Alu Mg	suitable		
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable only under restricted conditions		
INOX	suitable only under restricted conditions		
GG(G)	suitable only under restricted conditions		
CuZn	suitable		
Plastic, GRP	suitable		
Wood	suitable only under restricted conditions		
dry	suitable		

Accessories

Abrasive roll holder 6 mm shank Ø Mounting-Ø×Overall length 3X63 mm

553835 3X63