

Garant
**Clamping toolholder MCLNR 95°, for indexable inserts CN., right-hand,
Shank / insert size: 20/12mm**

Order data

Order number	250006 20/12
GTIN	4045197861535
Item class	21T

Technical description

Head length L_1	28 mm
Insert size	12 mm
ISO code toolholder	MCLNR/L 2020K12
Shim	259031 22
Shim screw	259025 6
Overall length L	125 mm
Screw for clamping claw	259021 1
Functional width L_4	25 mm
suitable indexable insert	CN.. 1204..
Shank size	20 mm
Clamping claw	259038 4
Standard	Works standard
Application type	right-hand
Through-coolant	no
Setting angle κ	95 degrees

Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Screw for clamping claw Type 1	259021 1
Shim screw Type 6	259025 6
Shim Type 22	259031 22
Clamping claw Type 4	259038 4
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15