

Garant
**Clamping toolholder MCLNR 95°, for indexable inserts CN., right-hand,
Shank / insert size: 25/16mm**

Order data

Order number	250006 25/16
GTIN	4045197861566
Item class	21T

Technical description

Clamping claw	259038 4
Screw for clamping claw	259021 1
Head length L ₁	33 mm
Functional width L ₄	32 mm
Shim	259031 23
Insert size	16 mm
Shank size	25 mm
Overall length L	150 mm
suitable indexable insert	CN.. 1606..
ISO code toolholder	MCLNR/L 2525M16
Shim screw	259025 7
Standard	Works standard
Application type	right-hand
Through-coolant	no
Setting angle κ	95 degrees

Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Screw for clamping claw Type 1	259021 1
Shim screw Type 7	259025 7
Shim Type 23	259031 23
Clamping claw Type 4	259038 4
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15