

Garant
Clamping toolholder PSBNL 75°, for indexable inserts SN., left-hand, Shank / insert size: 32/15mm

Order data

Order number	251107 32/15
GTIN	4045197862006
Item class	21T

Technical description

Shim punches pack	259047 4
ISO code toolholder	PSBNR/L 3232P15
suitable indexable insert	SN.. 1506..
Overall length L	170 mm
Lever screw	259018 11
Shank size	32 mm
Head length L ₁	32 mm
Shim	259031 37
Insert size	15 mm
Shim pins pack	259044 6
Functional width L ₄	27 mm
Lever	259015 12
Standard	Works standard
Application type	left-hand
Through-coolant	no
Setting angle κ	75 degrees

Application	External longitudinal turning
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15