



Burr Z3 - medium, with chip breaker, HSS, Type: M1020



Order data

Order number	540800 M1020
GTIN	4045197156204
Item class	52D

Description

Version:

Shank \varnothing 6 mm.

HSS burrs for difficult vibration applications. **Pointed cone shape**(SKM).

Application:

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning, weld and surface preparation.

Technical description

Shape description	pointed cone
Shape	M1020
Overall length	60 mm
Head \varnothing	10 mm
Shank \varnothing	6 mm
Tooth type abbreviation	Z3
Type of cut	with chip breaker
Toothing grit designation	medium
Head length	20 mm
Series	Tooth configuration Z3
Tool material	HSS
Type of product	Burr

