

Garant
Face mill arbor, HSK-A 100 A = 100, Spigot Ø d1: 50mm

Order data

Order number	306678 50
GTIN	4045197290458
Item class	31A

Description
Version:

- **Clamping Ø 40 with 4 tapped holes for drive blocks to DIN 2079.**
- **With Balluff/RFID chip bore.**
- **Increased collar contact surface.**
- **HSK mating faces machined.**

Application:

For clamping shell end mills and milling cutter heads.

Supplied with:

Lock screw

Optional extras:

Coolant tube No. 309880, socket wrench for coolant tubes No. 309890, toggle spanner No. 309840.

Technical description

Overhang dimension A	100 mm
Spigot Ø d ₁	50 mm
Suitable toggle spanner No. 309840	50
Spare milling cutter lock screw No. 309860 / 309861	50
Milling mandrel length L ₄	30 mm

External \varnothing D	120 mm
Clamping \varnothing D ₁	50 mm
Adapter	HSK-A 100 A = 100
Arbor standard	DIN 69882-3
Arbor standard	ISO 12164-1
Arbor standard	DIN 69893
Shape	A
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	$\leq 6 \mu\text{m}$
Machining strategy	HPC
Type of product	Milling head arbor

Accessories

Socket wrench for coolant tubes for HSK 50	309890 50
HSK coolant tube for HSK 50	309880 50
Milling cutter lock screw for mandrel \varnothing 50 mm	309860 50