



External blade micrometer, Measuring range: 75-100mm



Order data

Order number	421900 75-100
GTIN	4045197203984
Item class	42B

Description

Version:

With non-rotating spindle and flat blade anvils. Measuring spindle and anvil of hardened steel, controls and reading parts satin chrome-plated.

Supplied with:

From size 25-50 including 1 setting standard.

Technical description

Measuring range	75 - 100 mm
Flat blade anvils width	0.75 mm
Micrometer barrel graduations	1/50 mm
Spindle Ø	8 mm
Flat blade anvils length	6.5 mm
Spindle pitch	0.5 mm
Scale divisions	0.01 mm
Calibration	B2
Standard	DIN 863
Measurement technology	analogue
Packaging	sturdy box

Type of product	External micrometer
-----------------	---------------------

Services

Calibration External micrometer including setting dimension maximum measuring range 100 mm	022040 100
--	------------

DAkkS calibration External micrometer including setting dimension maximum measuring range 100 mm	022050 100
--	------------

Accessories

Micrometer setting standard overall length 75 mm	421100 75
--	-----------