



Centring square, Stock length: 70mm



Order data

Order number	455000 70
GTIN	4045197205971
Item class	42F

Description

Version:

Precision steel version with mm graduation on the beam. Functional faces precision ground, remaining faces precision machined.

Application:

For marking the centre point of round plates and shafts. Centre is marked crosswise 2 - 3 times.

Technical description

Error limit	0.3 arc min.
Beam graduations	100 mm
for maximum shaft \varnothing	90 mm
Slide beam cross section	12×4.0 mm
Stock length	70 mm
Standard	Manufacturer's standard
Material	Stainless steel, INOX
Calibration	F5
Type of product	Centring square

Services

Calibration Centring, angle, and mitre squares maximum arm length 300

025850 300