

**Garant**

**Steel boring bar A.. MVZNL 95°, for indexable inserts VN.., left-hand, Shank  
Ø / insert size: 40/16mm**


**Order data**

Order number	251729 40/16
GTIN	4045197868282
Item class	21T

**Technical description**

Setting angle $\kappa$	95 degrees
ISO code toolholder	A40T MVZNR/L 16
Minimum pre-drill $\varnothing D_{\min}$	57 mm
Insert size	16 mm
Shim screw	259025 3
Screw for clamp	259021 4
Shim	259031 39
Overall length L	300 mm
Overhang $L_1$	120 mm
Clamping height $L_2$	38.5 mm
Centre offset $L_3$	35 mm
Clamping claw	259038 2
suitable indexable insert	VN.. 1604..
Usable depth T	15 mm
Shank $\varnothing D_s$	40 mm
Standard	Works standard

Application type	left-hand
Boring depth up to	3×D
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring Bar

---

## Accessories

Screw for clamping claw Type 4	259021 4
Shim screw Type 3	259025 3
Shim Type 39	259031 39
Clamping claw Type 2	259038 2
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8