

Garant
Short drill chuck, PSC 40, Clamping range: 0,3-10mm

Order data

Order number	308587 0,3-10
GTIN	4045197868817
Item class	31B

Description
Version:

- **With RFID/Balluffchip bore.**
- **All shanks hard turned (for smooth running!).**
- **Mating faces of the PSC internal contour machined.**
- **For clockwise and anticlockwise rotation.**
- **Sand-blasted.**

Max. slim chucks for the most common \varnothing 0.3 – 10.2 mm.

Supplied with:

Clamping wrench.

Optional extras:

Coolant tube No. 309885; socket No. 309893.

Technical description

External \varnothing D	36 mm
Overhang dimension A	74 mm
Clamping range	0.3 - 10.2 mm
Spare chuck key No. 627425	4 AF
Adapter	PSC 40
Arbor standard	ISO 26623-1
Through-coolant	yes

Balance quality G at rotational speed	G 2.5 at 18,000 rpm
Concentricity	$\leq 3 \mu\text{m}$
maximum tightening torque $M_{d \max}$	$\leq 14 \text{ Nm}$
Type of product	Short drill chuck

Accessories

Hexagon screwdriver, with T-handle Hexagon 4 mm	627481 4
---	----------