

Garant
Slim hydraulic chuck, SK 40 A = 120, Clamping range \varnothing D1: 16mm

Order data

Order number	302093 16
GTIN	4045197868824
Item class	31A

Description
Version:

- **Extremely slim design (3° contour)**
- **Processed surface structure.**
- **With RFID/Balluffchip bore.**
- **Axial length adjustment possible.**
- **Shanks hard turned.**
- **Reducing adapters can be used.**

Application:

Especially for tool and mould making. **Wherever reduced interference contours are required.** For drilling, reaming, and milling. For clamping tools with shank tolerance h6.

Supplied with:

Hexagon socket drive with T-handle.

Optional extras:

Pull studs (AB) No. 308600 – 308806, AB pull stud wrenches No. 308820 / 308835, Reducing sleeves No. 302135 – 302187.

Technical description

\varnothing D ₂	24 mm
External \varnothing D	49.5 mm
L ₂	79 mm
\varnothing D ₃	32.3 mm
Clamping \varnothing D ₁	16 mm

Overhang dimension A	120 mm
Adapter	SK 40 A = 120
Arbor standard	ISO 7388-1
Shape	ADB
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	≤ 3 μm
Machining strategy	HPC
Machining strategy	HSC
Balluffchip bore	yes
Type of product	Hydraulic clamping chuck

Accessories

Pull studsealed, form B suitable for steep tapers 40	308620 40
Pull stud 60°sealed suitable for steep tapers 40	308785 40
Pull stud, 18CrNiMo7Form A suitable for steep tapers 40	308605 40
Pull stud 90°sealed suitable for steep tapers 40	308790 40
Special pull stud with internal thread suitable for steep tapers 40	308740 40
Pull studForm B suitable for steep tapers 40	308640 40
Pull stud 45°sealed suitable for steep tapers 40	308765 40
Pull studsealed, form A suitable for steep tapers 40	308610 40
Pull stud, 18CrNiMo7sealed, form B suitable for steep tapers 40	308615 40
Pull studsealed suitable for steep tapers 40	308635 40
Pull studMazak, form A suitable for steep tapers 40M	308670 40M
Pull stud Hurco 90° with fitsealed suitable for steep tapers 40	308806 40
Pull stud 45°sealed suitable for steep tapers 40	308760 40
	308820 40

Wrench for pull studs DIN ISO 7388-1 (formerly DIN 69872)
suitable for ISO taper size 40

Pull stud sealed suitable for steep tapers 40	308660 40
ER chuck key 1/2 inch socket for ER collet chuck 40	309700 40
Pull stud Mori-Seiki, sealed, form A suitable for steep tapers 40	308625 40
Pull stud Mori-Seiki, sealed, form A suitable for steep tapers 40	308630 40
Pull stud Form A suitable for steep tapers 40	308600 40
Wrench for pull studs ISO 7388 suitable for ISO taper size 40	308830 40
Special pull stud with no internal thread sealed suitable for steep tapers 40	308700 40
ER chuck key for ER collet chuck 40	309680 40
Hurco 45° pull stud with 4-mm bore and fit sealed suitable for steep tapers 40	308801 40
Pull stud 90° sealed suitable for steep tapers 40	308795 40
Pull stud sealed, form B suitable for steep tapers 40	308650 40
Pull stud Hurco 45° with fit sealed suitable for steep tapers 40	308802 40