

Garant
Burr Z FINE – very fine, Carbide, Type: A0820

Order data

Order number	540440 A0820
GTIN	4045197679901
Item class	51D

Description
Version:

 Shank \varnothing 6 mm.

GARANT burrs are manufactured from high performance carbide grades with high wear resistance and maximum cutting edge strength, using only the latest CNC machines. Steel shanks are used when the head diameter is larger than the shank diameter, otherwise they are made from solid carbide. **Cylindrical shape A (ZYA), without end cut.**

Application:

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning, weld and surface preparation.

Technical description

Shape	A0820
Tooth type abbreviation	Z FINE
Shape description	Cylindrical without end cut
Overall length	60 mm
Head \varnothing	8 mm
Toothing grit designation	very fine
Shank \varnothing	6 mm
Head length	20 mm
Series	Tooth configuration Z FINE
Tool material	Carbide

Type of product

Burr

User data

	Suitability	V_c	ISO code
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
INOX	suitable		
Ti	suitable		
GG(G)	suitable		