

Garant**Set of grinding points fine, AR, Number of grinding points: 10****Order data**

Order number	550100 10
GTIN	4045197239082
Item class	51E

Description**Version:**

GARANT grinding points (OSA certified and tested to DIN EN 12 413) are specially designed for hardness, bonding, grit type and grit size for the specific applications and cover a very wide application range. Minimal radial run-out ensures vibration-free grinding which is good for man, machine, and component. GARANT grinding points are generally suitable for **edge and surface grinding** and provide you with maximum material removal rates, long service life, and consistent surface finish quality of the component.

Shank \varnothing 3 mm \times 30 mm. Recommended circumferential speed 30 –50 m/s.

Ceramic bonded grinding points in **pink electro-carborundum (AR)**. Medium-hard version.

Assortment of grinding points in the most popular shapes and sizes.

Application:

For general-purpose grinding of **unalloyed and low-alloy** steels and **cast iron**.

Recommended cutting speed 30 – 50 m/s.

Supplied with:

1 each grinding point ZY0205 / ZY0306 / ZY0510 / ZY1303 / ZY1604 / KU06 / KU10 / SP0306 / D18 0708 / B53 0816.

Technical description

Number of grinding points	10
Grit designation	fine
Grinding media	Standard aluminium oxide (A)
Grinding medium code	A
Product name attribute	AR
Shank Ø	3 mm
Shaft length	30 mm
Type of product	Grinding point