


HOLEX
Flap wheel (A), 80 grit, Head Ø×head width: 50X15 mm

Order data

Order number	554200 50X15
GTIN	4045197240668
Item class	52E

Description
Version:

Flap strips bonded on to the shank of the tool.

Abrasive strips covered with **Aluminium Oxide (A)**.

Application:

Primarily for finish grinding and polishing tasks on larger radii in tool and mould making, for vessel and machine fabrication. The abrasive strips adapt to the contours of the component.

Grinding medium code: A

Shank Ø: 6 mm

recommended speed: 9000 rpm

maximum speed: 15300 rpm

Technical description

Head width	15 mm
Grit	80
maximum speed	15300 rpm
recommended speed	9000 rpm

Shank Ø	6 mm
Head Ø	50 mm
Grinding media	Aluminium Oxide grit (A)
Grinding medium code	A
Product name attribute	80 grit
Type of product	Flap wheel