

**Flap wheel Fleece sinusoidal, medium, Head Ø×head width: 80X50mm****Order data**

Order number	554976 80X50
GTIN	4045197678850
Item class	52E

Description**Version:**

Sinusoidal abrasive fleece without cut edges. Shank Ø 6 mm.

Application:

For matting and **polishing** without abrupt changes in texture.

Technical description

Head width	50 mm
recommended speed	4000 min ⁻¹
maximum speed	7000 min ⁻¹
Shank Ø	6 mm
Head Ø	80 mm
Grinding medium code	A
Grit equivalent	180
Grit designation	medium
Product name attribute	medium

Type of product

Flap wheel

User data

	Suitability	V_c	ISO code
Alu Mg	suitable only under restricted conditions		
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable only under restricted conditions		
Steel < 67 HRC	suitable only under restricted conditions		
INOX	suitable		
Ti	suitable only under restricted conditions		
GG(G)	suitable		
CuZn	suitable		
Plastic, GRP	suitable		
Wood	suitable		
Paint	suitable only under restricted conditions		
dry	suitable		