

**HOLEX****Fleece velour-backed abrasive disc, Ø 125 mm, Grit equivalent: 280****Order data**

Order number	566950 280
GTIN	4045197566256
Item class	52E

**Description****Version:**

Fleece velour-backed abrasive discs with through-stitched backing for hook and loop fastener. With removable centre for more precise positioning and attachment of the disc to the backing pad (**approx. 50 % reduction in vibration level with velour-backed abrasive discs No. 566965**).

**Application:**

On angle grinders with hook and loop fastener backing pad No. 566960 or 566965. For **finishing, matting, smoothing** with significant reduction in roughness, and for **light cleaning** (such as removal of discolouration) and **deburring tasks**.

**Note:**

See No. **567705ff** onwards for velour-backed abrasive discs for rough abrasion.

maximum circumferential speed: 40 m/s

Grit designation: fine

Version: A very fine

Colour: blue

**Technical description**

Version	A very fine
---------	-------------

Colour	blue
Grit equivalent	280
Grit designation	fine
Disc Ø	125 mm
Grinding medium code	A
Iron, sulphur and chlorine constituents	< 0.1 %
Product name attribute	Ø 125 mm
maximum circumferential speed	40 m/s
Type of product	Non-woven abrasive

### User data

	Suitability	V <sub>c</sub>	ISO code
Alu Mg	suitable		
Steel < 900 N/mm <sup>2</sup>	suitable		
Steel < 1400 N/mm <sup>2</sup>	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
INOX	suitable		
Ti	suitable		
GG(G)	suitable		
CuZn	suitable		
Plastic, GRP	suitable		
Wood	suitable		
Paint	suitable		
Uni	suitable		
wet maximum	suitable only under restricted conditions		
dry	suitable		

---

## Accessories

Hook and loop backing pad with Centring and M 14 thread  
External Ø 125 mm

566965 125

Hook and loop backing pad with Thread M 14 External Ø  
125 mm

566960 125