

HOLEX**Abrasive sleeve, conical (A) 40 grit coarse, largest sleeve \varnothing x sleeve width:
29X30mm**

Order data

Order number	553850 29X30
GTIN	4045197240583
Item class	52E

Description

Version:

Made of non-tearing, synthetic resin bonded material with long service life and good grit adhesion.

Aluminium Oxide (A) for general-purpose grinding work.

The rubber body of the abrasive sleeve holder expands at high speed to hold the abrasive sleeve in place. The full width of the sleeve can be used, it does not slip and can be replaced quickly and easily (twist in the direction of slots when fitting/removing). Only compatible with abrasive sleeve holders.

Application:

Abrasive sleeves are predominantly used for surface grinding tasks which require the removal of large amounts of material – even at sharp edges.

Suitable for:

Abrasive sleeve holder No. 553830.

Technical description

Sleeve width	30 mm
Grit	40

largest sleeve Ø	29 mm
Grit designation	coarse
Grinding media	Standard Aluminium Oxide
Grinding medium code	A
Sleeve shape	conical
Type of product	Abrasive sleeve

User data

	Suitability	V _c	ISO code
Alu Mg	suitable		
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable only under restricted conditions		
INOX	suitable only under restricted conditions		
GG(G)	suitable only under restricted conditions		
CuZn	suitable		
Plastic, GRP	suitable		
Wood	suitable only under restricted conditions		
dry	suitable		

Accessories

Abrasive sleeve holder slit, conical shank 6 mm Ø largest Øxhead length 29X30 mm

553830 29X30