

HOLEX
HOLEX Pro cutting disc "2 in 1", Disc Ø: 178mm

Order data

Order number	563500 178
GTIN	4045197593160
Item class	52M

Description
Version:
Universal cutting disc for steel and stainless steel.

Easy-cutting and stable.

Application:

 For freehand cutting using electric and pneumatic angle grinders with maximum 80 m/s peripheral cutting speed v_c .

Specification:
A30Q-BF.
Note:

The disc thickness should be at least 20% of the material thickness to be cut.

Technical description

Bore Ø	22.23 mm
maximum speed	8500 min ⁻¹
Shape description	flat
Shape	41

Disc thickness	2.5 mm
Specification	A30Q-BF
Disc Ø	178 mm
for material thicknesses	7.5 - 12.5 mm
Grinding medium code	A
Iron, sulphur and chlorine constituents	< 0.1 %
recommended approach angle	90 degrees
optimised for material	HSS
optimised for material	Steel
Propulsive equipment	Angle grinder
maximum circumferential speed	80 m/s
Type of product	Cutting disc

User data

	Suitability	V _c	ISO code
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable only under restricted conditions		
INOX	suitable only under restricted conditions		
Ti	suitable only under restricted conditions		
GG(G)	suitable only under restricted conditions		
dry	suitable		

Accessories

Pair of clamping flanges Flange Ø 76 mm

563990 76