

Garant

**Carbide boring bar E.. SDQCR 107,5°, for indexable inserts DC., right-hand,
Shank Ø / insert size: 10/07mm**


Order data

Order number	260320 10/07
GTIN	4045197877697
Item class	21T

Technical description

Clamping height L_2	9.6 mm
Minimum pre-drill $\varnothing D_{\min}$	13 mm
Centre offset L_3	7 mm
Overall length L	125 mm
Insert size	7 mm
suitable indexable insert	DC.. 0702..
Setting angle κ	107.5 degrees
ISO code toolholder	E10K SDQCR/L07
Pack of insert screws	269028 7
Overhang L_1	26.5 mm
Shank $\varnothing D_s$	10 mm
Standard	DIN 8024
Application type	right-hand
Boring depth up to	8xD
Tool material	Carbide
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring Bar

Accessories

Set of insert screws Type 7	269028 7
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8