



HOLEX Pro cutting disc "2 in 1", Disc Ø: 230mm



Order data

Order number	563500 230
GTIN	4045197593177
Item class	52M

Description

Version:

Universal cutting disc for steel and stainless steel.

Easy-cutting and stable.

Application:

For freehand cutting using electric and pneumatic angle grinders with maximum 80 m/s peripheral cutting speed v_c .

Specification:

A30Q-BF.

Note:

The disc thickness should be at least 20% of the material thickness to be cut.

Technical description

Shape description	flat
Bore Ø	22.23 mm
maximum speed	6600 min ⁻¹
Disc thickness	2.5 mm

Shape	41
Specification	A30Q-BF
Disc Ø	230 mm
for material thicknesses	7.5 - 12.5 mm
Grinding medium code	A
Iron, sulphur and chlorine constituents	< 0.1 %
recommended approach angle	90 degrees
optimised for material	HSS
optimised for material	Steel
Propulsive equipment	Angle grinder
maximum circumferential speed	80 m/s
Type of product	Cutting disc

User data

	Suitability	V _c	ISO code
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable only under restricted conditions		
INOX	suitable only under restricted conditions		
Ti	suitable only under restricted conditions		
GG(G)	suitable only under restricted conditions		
dry	suitable		

Accessories

Pair of clamping flanges Flange Ø 76 mm

563990 76