

Garant
Clamp toolholder, right-hand, Shank / insert size: 25/12mm

Order data

Order number	250006 25/12
GTIN	4045197861542
Item class	21T

Description

Clamp toolholder 25/12 mm ISO code toolholder: MCLNR/L 2525M12

suitable indexable insert: CN.. 1204..

Functional width L_4 : 32 mm

Head length L_1 : 33 mm

Overall length L: 150 mm

Shim: 259031 22

Technical description

Overall length L	150 mm
Head length L_1	33 mm
suitable indexable insert	CN.. 1204..
Insert size	12 mm
Clamping claw	259038 4
Shim	259031 22
Shank size	25 mm
Shim screw	259025 6
Screw for clamping claw	259021 1
ISO code toolholder	MCLNR/L 2525M12
Functional width L_4	32 mm

Series	QuickTurn
Application type	right-hand
Standard	DIN ISO 5610
Through-coolant	no
Setting angle κ	95°
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Shim screw	259177
Clamp	259322
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659906 500
Shim	259233
Clamping claw Type 4	259038 4
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15
Shim Type 22	259031 22
Shim screw Type 6	259025 6
Screw for clamping claw	259180
Screw for clamping claw Type 1	259021 1