

Garant

**Carbide boring bar E.. SDQCL 107,5°, for indexable inserts DC., left-hand,
Shank Ø / insert size: 16/07mm**

**Order data**

Order number	260321 16/07
GTIN	4045197877772
Item class	21T

Technical description

Minimum pre-drill Ø D_{min}	20 mm
Overhang L_1	49.5 mm
Centre offset L_3	10 mm
Insert size	7 mm
ISO code toolholder	E16R SDQCR/L07
Overall length L	200 mm
Pack of insert screws	269028 7
suitable indexable insert	DC.. 0702..
Clamping height L_2	15.6 mm
Setting angle κ	107.5 degrees
Shank Ø D_s	16 mm
Standard	DIN 8024
Application type	left-hand
Boring depth up to	8×D
Tool material	Carbide
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring Bar

Accessories

Set of insert screws Type 7	269028 7
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8