

Garant
**Clamping toolholder PSBNR 75°, for indexable inserts SN., right-hand,
Shank / insert size: 25/15mm**

Order data

Order number	251106 25/15
GTIN	4045197861948
Item class	21T

Technical description

Head length L ₁	32 mm
Shim	259031 37
Overall length L	150 mm
Shim pins pack	259044 6
Functional width L ₄	22 mm
Lever	259015 12
ISO code toolholder	PSBNR/L 2525M15
Insert size	15 mm
Shim punches pack	259047 4
Lever screw	259018 11
Shank size	25 mm
suitable indexable insert	SN.. 1506..
Standard	DIN ISO 5610
Application type	right-hand
Through-coolant	no
Setting angle κ	75 degrees

Application	External longitudinal turning
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15