

Garant
Clamping toolholder PSBNL 75°, for indexable inserts SN., left-hand, Shank / insert size: 25/12mm

Order data

Order number	251107 25/12
GTIN	4045197861986
Item class	21T

Technical description

Functional width L_4	22 mm
suitable indexable insert	SN.. 1204..
Overall length L	150 mm
Head length L_1	29 mm
Insert size	12 mm
Shim	259031 20
Lever screw	259018 2
Shank size	25 mm
Shim punches pack	259047 2
Shim pins pack	259044 2
Lever	259015 2
ISO code toolholder	PSBNR/L 2525M12
Standard	DIN ISO 5610
Application type	left-hand
Through-coolant	no
Setting angle κ	75 degrees

Application	External longitudinal turning
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
Precision Bit for hexagon, 1/4 inch E 6.3 Hexagon 3 mm	674242 3