


Garant**Flap wheel (CER), 80 grit, Head Ø×head width: 50X20mm****Order data**

| | |
|--------------|---------------|
| Order number | 554160 50X20 |
| GTIN | 4045197882813 |
| Item class | 51E |

Description**Version:**

Flap strips bonded on to the shank of the tool.
Abrasive strips covered with **ceramic grit (CER)**.

Application:

Primarily for finish grinding and polishing tasks on larger radii in tool and mould making, for vessel and machine fabrication. The abrasive strips adapt to the contours of the component.

Grinding medium code: Ceramic

Shank Ø: 6 mm

recommended speed: 9000 min⁻¹

maximum speed: 15300 min⁻¹

Technical description

| | |
|-------------------|-------------------------|
| Head Ø | 50 mm |
| Grit | 80 |
| maximum speed | 15300 min ⁻¹ |
| Shank Ø | 6 mm |
| recommended speed | 9000 min ⁻¹ |

| | |
|------------------------|--------------------|
| Head width | 20 mm |
| Grinding media | Ceramic grit (CER) |
| Grinding medium code | Ceramic |
| Product name attribute | 80 grit |
| Type of product | Flap wheel |

User data

| | Suitability | V _c | ISO code |
|--------------------------------|---|----------------|----------|
| Steel < 900 N/mm ² | suitable only under restricted conditions | | |
| Steel < 1400 N/mm ² | suitable | | |
| Steel < 55 HRC | suitable | | |
| Steel < 60 HRC | suitable | | |
| Steel < 67 HRC | suitable | | |
| INOX | suitable | | |
| Ti | suitable | | |
| GG(G) | suitable | | |
| CuZn | suitable | | |
| Plastic, GRP | suitable | | |
| Wood | suitable | | |
| dry | suitable | | |