

Garant**Burr, Carbide, Type: R1015****Order data**

Order number	541000 R1015
GTIN	4045197156266
Item class	51D

Description**Version:**

GARANT burrs are manufactured from high performance carbide grades with high wear resistance and maximum cutting edge strength, using only the latest CNC machines. Steel shanks are used when the head diameter is larger than the shank diameter, otherwise they are made from solid carbide. **Deburring head (external)** with radius for edge rounding.

Special deburrer shape (R), external.

Application:

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning, weld and surface preparation.

Note:

Reduced speed for burrs with an overall length of 120 mm: maximum 11,000 rpm

Technical description

Overall length	55 mm
Toothing grit designation	medium
Shape description	deburring

Shape	R1015
Tooth type abbreviation	Z3
Head Ø	10 mm
Shank Ø	6 mm
Radius	8 mm
Head length	15 mm
Series	Tooth configuration Z3
Tool material	Carbide
Type of product	Burr