



Burr Z3 – medium with chip breaker, HSS, Type: K1230



Order data

Order number	541200 K1230
GTIN	4045197156334
Item class	52D

Description

Version:

Special shapes: E, NS, K.

Shank Ø 6 mm. **Special shape K club** (K).

Application:

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning, weld and surface preparation.

Note:

Reduced speed for burrs with an overall length of 120 mm: maximum 11,000 rpm

Technical description

Shape description	club
Head Ø	12 mm
Shape	K1230
Overall length	70 mm
Shank Ø	6 mm
Tooth type abbreviation	Z3
Type of cut	with chip breaker
Toothing grit designation	medium
Head length	30 mm
Series	Tooth configuration Z3
Tool material	HSS

Type of product

Burr