

Garant**Circular saw blade, wood, alternating teeth medium, Blade Ø D: 165mm****Order data**

Order number	584035 165
GTIN	4045197883711
Item class	51S

Description**Version:**

Tipped with carbide inserts, precision version with high-strength blade, noise damped. Generously dimensioned carbide teeth allow multiple re-grinding.

Application:

For circular, cross-cut, compound, and mitre saws.

Type UW for **board materials, veneered or plastic coated on one side**, veneer packs longitudinally, hard paper and hard fabric.

Note:

Further circular saw blades can be found in Group 17.

Bore Ø: 20 mm

Number of teeth: 24

Width of cut B: 2 mm

Technical description

Bore Ø	20 mm
Blade Ø D	165 mm

Width of cut B	2 mm
Number of teeth	24
Type of product	Circular saw blade