

Garant

Circular saw blade, wood, alternating teeth universal, Blade Ø D: 230mm



Order data

Order number	584075 230
GTIN	4045197220882
Item class	51S

Description

Version:

Tipped with carbide inserts, precision version with high-strength blade, noise damped. Generously dimensioned carbide teeth allow multiple re-grinding.

Application:

For circular, cross-cut, compound, and mitre saws.

Universal circular saw blade with long tool life and low noise, **unaffected by nails**. For **all wood types** and difficult materials in the building trade, including aluminium sections

Note:

Further circular saw blades can be found in Group 17.

Bore Ø: 30 mm

Drive holes number/Ø/pitch circle: 2/7/42 and 2/10/154 mm

Number of teeth: 34

Width of cut B: 2.8 mm

Technical description

Blade Ø D	230 mm
Bore Ø	30 mm

Number of teeth	34
Width of cut B	2.8 mm
Drive holes number/Ø/pitch circle	2/7/42 and 2/10/154 mm
Type of product	Circular saw blade