

Garant
**Clamping toolholder MVPNL 117,5°, for indexable inserts VN., left-hand,
Shank / insert size: 25/16mm**

Order data

Order number	251709 25/16
GTIN	4045197867124
Item class	21T

Technical description

Head length L_1	41 mm
Functional width L_4	32 mm
ISO code toolholder	MVPNR/L 2525M16
Shim	259031 39
Overall length L	150 mm
suitable indexable insert	VN.. 1604..
Insert size	16 mm
Clamping claw	259038 2
Screw for clamping claw	259021 1
Shim screw	259025 3
Shank size	25 mm
Standard	Works standard
Application type	left-hand
Through-coolant	no
Setting angle κ	117.5 degrees

Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Screw for clamping claw Type 1	259021 1
Shim screw Type 3	259025 3
Shim Type 39	259031 39
Clamping claw Type 2	259038 2
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8