

**Garant**

**Steel boring bar A.. MVUNL 93°, for indexable inserts VN.., left-hand, Shank  
Ø / insert size: 25/16mm**


**Order data**

Order number	251725 25/16
GTIN	4045197868220
Item class	21T

**Technical description**

ISO code toolholder	A25R MVUNR/L 16
Clamping claw	259038 4
Overall length L	200 mm
Setting angle $\kappa$	93 degrees
Shim screw	259025 3
Insert size	16 mm
Shim	259031 39
Minimum pre-drill $\varnothing D_{\min}$	32 mm
suitable indexable insert	VN.. 1604..
Clamping height $L_2$	24 mm
Centre offset $L_3$	17 mm
Screw for clamp	259021 4
Shank $\varnothing D_s$	25 mm
Standard	DIN 8024
Application type	left-hand
Boring depth up to	3xD

Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring Bar

---

## Accessories

Screw for clamping claw Type 4	259021 4
Shim screw Type 3	259025 3
Shim Type 39	259031 39
Clamping claw Type 4	259038 4
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8