

**Garant**
**Slim hydraulic chuck, HSK-E 40 A = 85, Clamping  $\varnothing$  D1: 5mm**

**Order data**

|              |               |
|--------------|---------------|
| Order number | 307526 5      |
| GTIN         | 4045197868435 |
| Item class   | 31A           |

**Description**
**Version:**

- **Extremely slim design (3°-contour).**
- **With RFID/Balluffchip bore.**
- **Axial length adjustment possible.**
- **Shanks hard turned.**
- **Reducing adapters can be used.**

**Advantage:**

- **Temperature-resistant due to completely enclosed system, i.e. no soldered pressure chambers.**
- **Ideal damping characteristics.**
- **High transmissible torques, providing high process reliability.**

**Application:**

Especially in operations in toolmaking and mould making.

**Wherever reduced interference contours are required.**

For drilling, reaming and milling

For clamping tools with shank tolerance h6.

**Supplied with:**

Hexagon key with T-handle.

**Optional extras:**

Reducing sleeves No. 302135 – 302165.

**Technical description**

|                          |       |
|--------------------------|-------|
| External $\varnothing$ D | 34 mm |
|--------------------------|-------|

|                                       |                          |
|---------------------------------------|--------------------------|
| Overhang dimension A                  | 85 mm                    |
| Clamping $\varnothing D_1$            | 5 mm                     |
| $\varnothing D_2$                     | 11 mm                    |
| $L_2$                                 | 45 mm                    |
| $\varnothing D_3$                     | 15.7 mm                  |
| Adapter                               | HSK-E 40 A = 85          |
| Arbor standard                        | DIN 69893                |
| Arbor standard                        | ISO 12164-1              |
| Shape                                 | A                        |
| Balance quality G at rotational speed | G 2.5 at 25,000 rpm      |
| Concentricity                         | $\leq 3 \mu\text{m}$     |
| Machining strategy                    | HSC                      |
| Machining strategy                    | HPC                      |
| Balluffchip bore                      | yes                      |
| Type of product                       | Hydraulic clamping chuck |