

HOLEX

Double-ended ring spanner set, deeply cranked, chrome-plated, Number of keys: 10



Order data

Order number	615960 10
GTIN	4045197331373
Item class	62A

Description

Version:

Drop-forged. With close tolerance jaw widths.

HOLEX – With oval shaft.

Standard:

DIN 838 / ISO 3318

Material:

HOLEX – Chrome vanadium steel, chrome-plated.

Supplied with:

1 each double ended ring spanner No. 615600 / 615000 / 615900 / 615950: 6x7; 8x9; 10x11; 12x13; 14x15; 16x17; 18x19; 20x22; 21x24; 27x30

Technical description

Number of keys	10
Width across flats	metric
Ring setting	75 degrees
Manufacturing process	drop forged
Material	Chrome vanadium steel
Surface	chrome plated

Product name attribute	chrome-plated
Type of product	Spanner

Accessories

Double-ended ring spanner, deeply cranked Width across flats 20X22 mm	615950 20X22
Double-ended ring spanner, deeply cranked Width across flats 8X9 mm	615950 8X9
Double-ended ring spanner, deeply cranked Width across flats 16X17 mm	615950 16X17
Double-ended ring spanner, deeply cranked Width across flats 27X30 mm	615950 27X30
Double-ended ring spanner, deeply cranked Width across flats 6X7 mm	615950 6X7
Double-ended ring spanner, deeply cranked Width across flats 12X13 mm	615950 12X13
Double-ended ring spanner, deeply cranked Width across flats 21X24 mm	615950 21X24
Double-ended ring spanner, deeply cranked Width across flats 10X11 mm	615950 10X11
Double-ended ring spanner, deeply cranked Width across flats 18X19 mm	615950 18X19
Double-ended ring spanner, deeply cranked Width across flats 14X15 mm	615950 14X15