

Garant
Face mill arbor with cooling channel bore, HSK-A 100 A = 130, Spigot Ø d1: 16mm

Order data

Order number	306686 16
GTIN	4045197870117
Item class	31A

Description
Version:

- Clamping Ø 40 with 4 tapped holes for drive blocks to DIN 2079.
- With Balluff/RFID chip bore.
- Increased collar contact surface.
- HSK mating faces machined.

With cooling channel bores.

Application:

For clamping shell end mills and milling cutter heads.

Supplied with:

Lock screw.

Optional extras:

Coolant tube No. 309880, socket wrench for coolant tubes No. 309890, toggle spanner No. 309840.

Technical description

Spare milling cutter lock screw No. 309860 / 309861	16
Milling mandrel length L ₄	17 mm
Overhang dimension A	130 mm
External Ø D	38 mm

Suitable toggle spanner No. 309840	16
Spigot $\varnothing d_1$	16 mm
Clamping $\varnothing D_1$	16 mm
Adapter	HSK-A 100 A = 130
Arbor standard	ISO 12164-1
Arbor standard	DIN 69882-3
Arbor standard	DIN 69893
Shape	A
Cooling channel bore	not pluggable
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	$\leq 6 \mu\text{m}$
Machining strategy	HPC
Type of product	Milling head arbor

Accessories

Toggle spanner for mandrel $\varnothing 16 \text{ mm}$	309840 16
Milling cutter lock screw for mandrel $\varnothing 16 \text{ mm}$	309860 16
Bolt for T-nuts for spigot $\varnothing D1 16 \text{ mm}$	309896 16
Half-round T-nut for face mill arbors For size 16	309898 16