

Garant
Grinding disc (CER), Ø 50.8 mm, Grit: 80

Order data

Order number	554012 80
GTIN	4045197526014
Item class	51E

Description
Version:

The Roloc™, Combidisc® CDR **quick-change system** with a plastic thread permits safe abrasive tool changing “with a single twist of the wrist” in a very short time.

Very high material removal rate and service life due to the use of self-sharpening ceramic grit (CER).

Application:

Use in conjunction with hard support pad No. 554089.

For efficient abrasion of small areas, even with changing contours. Reduced tool changing times save costs on multi-stage operations.

Note:

Roloc™ bristle discs can be found from No. 573510 onwards.

Grinding medium code: Ceramic

maximum speed: 25000 min⁻¹

Technical description

Grit	80
Disc Ø	50.8 mm

Grinding media	Ceramic grit (CER)
Grinding medium code	Ceramic
Grinding media backing	Fibre underlay
Product name attribute	Ø 50.8 mm
maximum speed	25000 min ⁻¹
Type of product	Grinding wheel

User data

	Suitability	V _c	ISO code
Alu Mg	suitable only under restricted conditions		
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
INOX	suitable		
Ti	suitable only under restricted conditions		
GG(G)	suitable		
CuZn	suitable		
dry	suitable		

Accessories

Rubber backing pad shank Ø 6 mm soft External Ø 50 mm	554091 50
Rubber backing pad shank Ø 6 mm hard External Ø 50 mm	554089 50
Rubber backing pad shank Ø 6 mm medium hard External Ø 50 mm	554093 50
	554092 50

Rubber backing pad shank Ø 6 mm medium External Ø 50 mm

Plastic backing pad shank Ø 6 mm External Ø 50 mm

554090 50