

**Garant****Indexable insert for turning VNGA 160404, CBN (0°), Cutting edge version: G****Order data**

Order number	255463 G
GTIN	4045197895431
Item class	21H

**Description****Version:**

Fitted with 2 cutters.

**Description:**

New type of CBN with a balanced combination wear-resistance and tensile strength for general-purpose use in hardened steel up to 67 HRC in combination with a special constitution. For use both in continuous cutting and also in slightly interrupted and heavily interrupted cutting.

**Technical description**

Grade	BU7220
Cutting edge version	G
Tool material	CBN
Finishing/roughing assignment	Finishing
Cutting speed $v_c$ main application	90 - 140 m/min
Feed $f$	0.05 - 0.15 mm/rev.

Cutting depth $a_p$	0.05 - 0.2 mm
Cutting conditions	continuous
Cutting conditions	heavily interrupted
Cutting conditions	slightly interrupted
Corner radius	0.4 mm
ISO code indexable insert	VNGA 160404
Number of changes/inserts	2
Product name attribute	BU7220
Type of product	Indexable insert for turning

### User data

	Suitability	$V_c$	ISO code
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
continuous	suitable		
irregular	suitable		
interrupted	suitable		
dry	suitable		