

Garant**Indexable insert for turning DNGA 110408, CBN (0°), Cutting edge version: G**

Order data

Order number	255442 G
GTIN	4045197895271
Item class	21H

Description

Version:

Fitted with 2 cutters.

Description:

New type of CBN with a balanced combination wear-resistance and tensile strength for general-purpose use in hardened steel up to 67 HRC in combination with a special constitution. For use both in continuous cutting and also in slightly interrupted and heavily interrupted cutting.

Technical description

Tool material	CBN
Cutting depth a_p	0.05 - 0.2 mm
Grade	BU7220
Cutting speed v_c main application	90 - 140 m/min
Feed f	0.05 - 0.15 mm/rev.
Cutting edge version	G

Cutting conditions	continuous
Cutting conditions	heavily interrupted
Cutting conditions	slightly interrupted
Corner radius	0.8 mm
Finishing/roughing assignment	Finishing
ISO code indexable insert	DNGA 110408
Number of changes/inserts	2
Product name attribute	BU7220
Type of product	Indexable insert for turning

User data

	Suitability	V_c	ISO code
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
continuous	suitable		
irregular	suitable		
interrupted	suitable		
dry	suitable		