

**Garant****Mini burr Z5 – fine, Carbide, Type: D0605****Order data**

Order number	546800 D0605
GTIN	4045197156556
Item class	51D

**Description****Version:**

**GARANT** burrs are manufactured from high performance carbide grades with high wear resistance and maximum cutting edge strength, using only the latest CNC machines. Steel shanks are used when the head diameter is larger than the shank diameter, otherwise they are made from solid carbide.

Carbide mini burr with shank  $\varnothing$  3 mm. **Ball shape** (KUD)

**Application:**

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning, weld and surface preparation.

**Technical description**

Toothing grit designation	fine
Tooth type abbreviation	Z5
Shape description	Ball
Overall length	35 mm
Head $\varnothing$	6 mm
Shape	D0605
Shank $\varnothing$	3 mm
Head length	5 mm
Series	Tooth configuration Z5
Tool material	Carbide

Type of product

Burr

**User data**

	<b>Suitability</b>	<b>V<sub>c</sub></b>	<b>ISO code</b>
Steel < 900 N/mm <sup>2</sup>	suitable		
Steel < 1400 N/mm <sup>2</sup>	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable only under restricted conditions		
INOX	suitable only under restricted conditions		
Ti	suitable only under restricted conditions		
GG(G)	suitable only under restricted conditions		